

Product Name :
PARAFFIN WAX BATH**Product Code :**
PEEHC10008**Description :**

PARAFFIN WAX BATH Internal wax tank made out of stainless steel sheet. The top has a aluminum cover and the edges of the bath has a laminated wooden rim, works on electricity 220-240 V. Provided with special wax immersion type heater and thermostat to control temperature. Externally finished oven baked. Wax Chamber size 50cm x 35cm x 25cm., Comes with Six kg wax. SPECIFICATIONS: Construction: Double walled effectively insulated. Wax tank of 20 gauge Stainless steel sheet. Fitted with laminated wooden rim & anodized Aluminium cover Mounted on 5cm dia. Four casters. Heaters: Two, 1kw each, special wax Heaters. Heat Control: Thermostat to control temperature from 30 to 110 deg.Cen. Finish: Externally finished in Oven Baked. Accessories: 6 Kg. Paraffin Wax, Power Plug, One brush for wax application & aluminium sheet mesh for heaters