

**Product Name :**  
OIL BATH (High temperature)**Product Code :**  
NMCBS11011**Description :**

OIL BATH (High temperature) Double wall construction. Inner chamber made of highly polished stainless steel sheet and the outer is made of mild sl duly finished in white stoving enamel/powder coated paint with mat finished colour combinations.

**Technical Specification :**

Temperature range 50 $\pm$ 1/2 C to 250 $\pm$ 1/2 C, 2 $\pm$ 1/2 C is controlled by a thermostat. Supplied complete with stirrer, diffuser shelves, cover etc. Specification OIL BATH Chamber Size a) 250x250x250 mm (10x10 $\pm$ 1/2x10 $\pm$ 1/2) b) 300x300x250 mm (12 $\pm$ 1/2x12 $\pm$ 1/2x10 $\pm$ 1/2) C) 350x350x250 mm (14 $\pm$ 1/2x14 $\pm$ 1/2x10 $\pm$ 1/2) Optional (i) Mercury contact thermometer and relay with accuracy better than 1 $\pm$ 1/2 C. (ii) Imported Thermostat with an accuracy of 1 $\pm$ 1/2 C (iii) Digital temp. indicator-cum-Controller. (iv) Microprocessor PID digital temp. indicator-cum-controller.