

Product Name :
Justice Auto Lensometer

Product Code :
NMCBS139013



Description :

Justice Auto Lensometer The only lensometer equipment at present that can measure accurately the low-degree lens below ± 0.12 in the country ± 0.12 The lensometer equipment that can measure accurately the colored lens with a degree of transparency of 10% ± 0.12 The lensometer equipment that can accurately and quickly measure the progressive lens. ± 0.12 The only lensometer equipment that can display the pupil diameter ± 0.12 Besides, the equipment can measure the pupil distance, and is equipped with UV meter and built-in thermosensitive printer ± 0.12 It is characterized with fast measuring speed, clear interface, convenient operation, accuracy and good repeatability etc. Specifications: Sphere 0 to $\pm 25D$ (0.01D, 0.12D, 0.25D steps) Cylinder 0 to $\pm 10D$ (0.01D, 0.12D, 0.25D steps) Axis 0-180 ± 1 (1 ± 0.5 steps) ADD 0 to 10D (0.01D, 0.12D, 0.25D steps) Prism 0 to 10 (0.01D, 0.12, 0.25 steps) Step 0.01D PD 80mm (Optional) Lens Diameter Max. approx. 120mm UV Out in UV (Optional) Compensation of Abbe number rang: 20 to 60 Measurable >10% and over (20% and over $\pm 15D$ to $\pm 25D$) Contact lenses 0 to $\pm 25D$ B.C. 6.00 to 9.00 Display Full graphic LCD with back light (Black/White) 320 \times 240 Printer Built-in thermosensitive printer, paper size 38mm (Optional) Power source 100-120V ~ / 200-240V ~ choosing 50 or 60HZ Weight 7Kg Power AC220V/50HZ, AC110V/60Hz, 40W# Justice Auto Lensometer, ENT Equipment exporters, ENT Equipment manufacturers

