

**Product Name :**  
3.5V COAXIAL OPHTHALMOSCOPE**Product Code :**  
NMCBS139046**Description :**

3.5V COAXIAL OPHTHALMOSCOPE Halogen HPX TM lamp provides 30% brighter, whiter light output than standard lamps for true tissue color and consistent, long-lasting illumination. Coaxial optics produce a shadow-free spot, easier entry into undilated pupils, and a larger field of view. Polarizing filter virtually eliminates corneal reflection. Red-free filter may be used with any aperture. Sealed optics keep out dust and dirt for years of maintenance-free operation. Rubber brow rest prevents scratching of eyeglasses. 28 focusing lenses with a range of -25 to +40 diopters. 68 focusing lenses with a range of -25 to +40 diopters. 3.5V COAXIAL OPHTHALMOSCOPE, ENT Equipment exporters, ENT Equipment manufacturers

**NAUGRA<sup>®</sup>****Medical Hospital Equipments Manufacturers****Website:**Medical Hospital Equipments Manufacturers,