

**Product Name :**  
HUMIDITY CABINET**Product Code :**  
NMCBS11021**Description :**

HUMIDITY CABINET Temperature range ambient temperature to 60° C. Temperature 1° C with built-in horizontal shape thermometer. The humidity is controlled by Humidistart from atmospheric humidity num/Stainless steel and outside Mild steel painted in epoxy powder coating. The door has glass window. To work on 220/230 volts A.C. Inside water tank is made of stainless steel. Specification :- HUMIDITY CABINET Chamber Inside Chamber (Size) CAPACITY 455 x 455 x 455 mm 95 ltrs 455 x 455 x 710 mm 147 ltrs 605 x 605 x 605 mm 225 ltrs 605 x 605 x 910 mm 335 ltrs OPTIONAL (i) Hygrometer (Humidity indicator). (ii) Digital temperature controller-cum-indicator. (iii) Imported thermostat  
• German with the accuracy of 0.5° C. (iv) Microprocessor PID digital temp. Indicator-cum-controller. (v) Automatic electronic controller with digital display for Temp.& Humidity combined. (vi) Automatic voltage stabilizer 3 KVA (recommended). Make Ajanta HUMIDITY CABINET, Heat And Refrigeration System Exporters, Heat And Refrigeration System Manufacturers