

Product Name :
OT Light Reflector**Product Code :**
NMCBS113003**Description :**

OT Light Reflector We are engaged in offering our clients with OT Light Reflector that are available in different models and sizes at market leading prices. These are designed in compliance with international quality norms & standards, using high-grade raw material and latest technology. We also check all the products on certain parameters to ensure flawlessness. Other information: A Dome Head: 515mm Dia Halogen Bulbs: 4 nos. 12v x 50 watt Light intensity at 1 mt.: 70,000 Lux Intensity Control: 4 Stage Height Adjustment: 600mm Action Radius: 1850mm Possible Movements: Radial, Angular & Axial Color Temperature: 4200 K \pm 300K Temp. rise in field: $3\frac{1}{2}$ - $6\frac{1}{2}$ c from Amb.Temp Low voltage unit with CVT: 1 No. (C.V.T optional) Input supply voltage: 220 volt A.C \pm 10% 50Hz \pm 2% Dimensions: B Dome Head: 515mm Dia. Halogen Bulbs: 4nos. 12v x 50 watt Light intensity at 1 mt.: 70,000 Lux Intensity Control: 4 Stage Height Adjustment: 550mm Action Radius: 1550mm Possible Movements: Radial, Angular & Axial Color Temperature: 4200 K \pm 300K Temp. rise in field: $3\frac{1}{2}$ - $6\frac{1}{2}$ c from Amb.Temp Low voltage unit with CVT: 1 No. (C.V.T optional) Input Supply Voltage: 220volt A.C \pm 10% 50Hz \pm 2% OT Light Reflector, Operation Theater Lights exporters, Operation Theater Lights manufacturers